

❖ BM-500 CL / BB-500 CL

Progressive Scan



PRELIMINARY

- **Member of C3 Basic series**
- **2456 (h) x 2058 (v) 3.45 μ m square pixels**
- **2/3" progressive scan – Monochrome and Bayer mosaic color versions**
- **15 frames/second with full resolution in continuous operation**
- **15 frames/second with external trigger and full resolution**
- **Increased frame rate with vertical binning (BM-500 CL) and partial scan**
- **Pre-Select and Pulse Width trigger modes**
- **Exposure time from 64 μ s to 2 sec. using Pulse Width trigger mode**
- **Programmable exposure from 64 μ s to 66 ms in Full Frame scan**
- **Several pre-processing functions for offloading host PC**
- **LVAL-synchronous/-asynchronous operation (auto-detect)**
- **Auto iris lens video output allows a wider range of light**
- **Camera Link interface with 12, 10 or 8-bit output**
- **Setup by Windows NT/2000/XP via Serial Communications**




Specifications for BM-500 CL / BB-500 CL

Specifications	BM-500 CL / BB-500 CL
Sensor	2/3" progressive scan CCD
Pixel Clock	60 MHz
Frame rate full frame	15 frames/second
Active area	8.47 (h) x 7.10 (v)
Cell size	3.45 (h) x 3.45 (v)
Active pixels	2456 (h) x 2058 (v)
Color (BB-500 CL)	Raw Bayer output, host based interpolation
Read-out modes	
Full	2456 (h) x 2058 (v) 15 fps
1/2 partial scan	2456 (h) x 1028 (v) 24 fps
1/4 partial scan	2456 (h) x 514 (v) 34 fps
1/8 partial scan	2456 (h) x 258 (v) 43 fps
2/3 partial scan	2456 (h) x 1372 (v) 20 fps
Vertical binning	2456 (h) x 1039 (v) 22 fps*
	*Note: BM-500 CL only
Sensitivity (BM-500 CL)	0.34 Lux (On sensor, max. gain, shutter off, 50% video)
Sensitivity (BB-500 CL)	1.0 Lux (On sensor, max. gain, shutter off, 50% video)
S/N ratio	>50 dB (0 dB gain)
Video output	Camera Link, 8-bit, 10-bit or 12-bit
Auto-iris lens video output	0.7 VP-p, enabled by internal switch
Gain	Manual Range -3 to 12 dB
Gamma/Knee	Look Up Table (LUT)
White balance (BB-500 CL)	Auto/Manual Pre-set (3200K, 4600K, 5600K)
Synchronization	Internal X-tal
Inputs	Camera Link TTL Ext. trigger, LVDS (CC 1) Ext. trigger 4V ±2V
Outputs	Camera Link TTL Clk., FVAL, LVAL, Data, EEN XEEN
Trigger modes	Pre-Select, Pulse Width
Electronic shutter	
Pre-set shutter	1/15 and 1/30 to 1/10,000 in 10 steps
Programmable exposure (PE)	2L(64µs) to 2072 L (66.44ms) in 1L steps
Pulse Width	max. 2 sec. (Can be set by 100µs unit or Pixel Clock unit)
Accumulation	Auto-detect LVAL-synchr. / asynchr.
Pre-processing functions	Output transfer functions (Gamma, multiple-point knee), Bayer white balance, L/R channel balancing, Blemish compensation
Control interface	Camera Link serial communication
Functions controlled by serial communication	Shutter, Trigger mode, Readout mode, Trigger Polarity, Black level, Gain, Pre-processing
Indicators on rear panel	LED for power and trigger input
Operating Temperature	-5°C to +45°C
Humidity (operation)	20 - 90% non-condensing
Storage temp./humidity	-25°C to +60°C / 20 to 90%
Vibration	10 G (20Hz to 200 Hz XYZ)
Shock	70 G
Regulations	CE (EN 61000-6-2, EN-61000-6-3), FCC part 15 class B, RoHS/WEEE
Power	12V DC +/-10%. 5.5W
Lens mount	C-mount
Dimensions (H x W x L)	55 x 55 x 55
Weight	200 g

Connector pin-out

DC In / Trigger



HIROSE HR10A-10R-12PB-01

Pin	Signal
1	GND
2	+12V DC input
3	GND
4	Iris Video
5	GND
6	NC
7	NC
8	GND
9	XEEN out
10	Trigger in*
11	DC +12V
12	GND

*) Selectable via CL or 12-pin Hirose

Note: Factory default is trigger via Camera Link


Camera Link interface




Pin	Signal	Function
1 14	GND	-
2 15	-/+ TxOUT0	CL Data
3 16	-/+ TxOUT1	CL Data
4 17	-/+ TxOUT2	CL Data
5 18	-/+ TxClk	CL clk
6 19	-/+ TxOUT3	CL Data
7 20	+/- RXD	Serial in
8 21	-/+ TXD	Serial out
9 22	CC1-/CC1+	Ext. trig*
10 23	CC2-/CC2+	Not used
11 24	CC3-/CC3+	Not used
12 25	CC4-/CC4+	Not used
13 26	GND	-

Dimensions


Front view




Side view




Bottom view




Rear view



Spectral Response BM-500 CL



Spectral Response BB-500 CL



Ordering Information

BM-500 CL 2/3" Monochrome Progressive Scan Camera
BB-500 CL 2/3" Bayer Mosaic Color Progressive Scan Camera

C3 Camera Suite Unlimited Digital Switchability

Europe, Middle East & Africa
Phone +45 4457 8888
Fax +45 4491 8880

Asia Pacific
Phone +81 45 440 0154
Fax +81 45 440 0166

Americas
Phone (Toll-Free) 1 800 445 5444
Phone +1 408 383 0300



See the possibilities

Visit our web site on www.jai.com